

### SIANG SYUAN FU ENTERPRISE CO., LTD

Address : No.230,Nanxuan Rd.,Hemei Township,Changhua County 50849,TaiwanTEL : 886-4-7561316FAX : 886-4-7567683Website : www.ssf-tw.comE-mail:info@ssf-tw.com

# ALL NEW 36X OUTSTANDING ADHESIVE AND SEALANT DISPENSER

With extra powerful thrust ratio, 36X series enables to dispense high-viscosity materials such as PU, epoxy...etc. Even used it in cold weather or low temperature working area, it can offer the excellent performance. Its high performance 36:1 thrust ratio mechanism enables to reduce user's hand and wrist strength and allows users to dispense high viscosity materials at ease. No matter how stiff your sealants are, it can extrude it effortlessly. For heavy-duty use, users can consider this series. Its high-end level performance may meet users' demand.

The feature of this series is that its *handle and trigger are both made with highquality aluminum alloy.* The surface is treated by liquid coating. It ensures long durability, better abrasion resistance and corrosion resistance. Also, make it more aesthetic.

This series also has single component, dual component, sachet component and bulk component version.

Except for dual component version, other three types are all equipped with patented **360° rotary type of carriage/barrel**. Due to the patented spacer design on it, both handle and carriage can be rotated 360-degree smoothly. When caulking meets around corners or turns, this function helps you easily change the caulking angle through rotating its handle or carriage, so that you can keep the caulk line be straight without interruption. No matter how you rotate it, the feeling will be the same!

This series is also equipped with a *patented no trigger gaps design* which is the function that we develop at our flagship version premium series. How does this function work? When there is too much free play on the trigger, it will automatically have no free play on the trigger. Even though it's used for a long term, the trigger has still no free play. It means when we squeeze the trigger, the sealants will immediately extrude out so as to offer precise dispensing and extends tool life.



## SIANG SYUAN FU ENTERPRISE CO., LTD

Address : No.230,Nanxuan Rd.,Hemei Township,Changhua County 50849,TaiwanTEL : 886-4-7561316FAX : 886-4-7567683Website : www.ssf-tw.comE-mail:info@ssf-tw.com

Here is one of our 36X series single caulking gun that we would like to specially recommend.

SSF-CK-S02M-1 is an updated version of SSF-CK-R02-1. If you want to divide different ranges of the product for your customers. For standard one (less expensive), you can choose SSF-CK-R02-1. For high-end level, you can choose this one. It has heat treatment chrome plated push rod ensures durability and long lifespan when you squeeze the high-viscosity sealant. We ever tested it under 150kgs testing spring (pretended it as high viscous sealants), the rod won't have the bite mark. The carriage is made with steel argon welding which has strong structure for long term using.

#### Patented rod puller with detachable cartridge cutter

For single component dispenser, sachet component and bulk component, users can choose to assemble a handy rod puller with cartridge cutter. It's convenient to cut the threaded nipples of cartridge and nozzle at a perfect angle. It can also be detached from the push rod for individual use.

#### **Optional patented protect case design**

The protect case that can be chosen. It can cover the handle and prevent dusty in parts.

#### **OEM** service

For customization, we also provide other push rod choice and LOGO screen printing to let you design a self-brand tool.

#### Versatile rod puller choice

Patented 2-in-1 convertible rod puller
(can be 180° expanding or folded as a J-shaped rod puller)
Patented rod puller with detachable cartridge cutter
(handy cartridge cutter to cut the threaded nipples of cartridge or nozzle as needed and can be detached from the push rod for individual use)
J-shaped ladder hook puller
(hang it on the ladder, belt or scaffolding when not in use)

Hall 4.1 Booth No. F088/ G089